



Offset Pull Handles



Oval / Square Bar Pull Handles



Standard

Type	Material	Surface Treatment
UHFN	SS400	Chrome Plating
UHFNS	SUS304	Buffing
UHFNA	Aluminum	Buffing
UHFNEA	Aluminum	Clear Anodize
UHFNB	Aluminum Alloy	Electrostatic Paint (Mat Black)

• For washers sold separately, refer to P.1180.

No Washer

With Washer

RoHS10

No Washer

Part Number Type	L	L1	Allowable Load (N)	Reference Mass (g)	UHFN	UHFNS	UHFNA	UHFNEA	UHFNB
48	58	2000	90						
66	76		100						
88	98		114						
100	110		122						
110	120		127						
120	130		134						
125	135		136						
160	170		158						

With Washer

Part Number Type	L	Washer Selection	L1	Allowable Load (N)	Reference Mass (g)	UHFNZ	UHFNSZ	UHFNAZ	UHFNEAZ	UHFNBZ
48	G	58	90							
66	(SUM22L + Chrome Plating)	76	100							
88		98	114							
100	B	110	122							
110	(SUM22L + Electrostatic Paint (Black))	120	127							
120		130	134							
125	S	135	136							
160	(SUS304)	170	158							

Ordering Example: Part Number - Washer Selection
 UHFN66 - G
 UHFNZ100 - G

Small Diameter

UHFNSC

Material: SUS304, Surface Treatment: Buffing

Part Number Type	L	D	H	A	d	M	Allowable Load (N)	Reference Mass (g)	Unit Price (1-9 pc (s))	Volume Discount Rate (10-49)	Volume Discount Rate (50-99)	Volume Discount Rate (100-200)
60	30	6	16	7	4	392	23					
80	31.5						28					
100	32						54					
120	40						70					

Ordering Example: Part Number
 UHFNSC80

Oval Bar Type

Type	Material	Surface Treatment
UABL	Aluminum Alloy	Tumble Polish
UABR	Aluminum Alloy	Electrostatic Paint (Mat Black)
UABLA	Aluminum Alloy	Buffing
UABLC	SUM22L or SUM24L	Chrome Plating
UABS	SUS304	Sandblasting

Part Number Type	A	L	L1	Lf	H	h	M (Coarse)	Allowable Load (N)	Unit Price (UABL, UABR, UABLA, UABLC, UABS)
20	100	113	10	47	34	M6	1100		
	112	125		49	36		700		
	120	133		51	38		600		
	128	141		53	36		470		
	160	173		55	38		2300		
26	112	129	12	57	40	M8	1400		
	120	137					1200		
	128	145					600		
	160	177					500		
	180	197					470		
	192	209					380		
	300	317					300		
	350	367							
	400	417							

Ordering Example: Part Number - L
 UABL20 - 100

Square Bar Pull Handles - L Fixed

Type	Material	Surface Treatment
USAN	SS400	Chrome Plating
USANS	SUS304	Buffing
USANA	Aluminum Alloy	Buffing
USANB	Aluminum Alloy	Electrostatic Paint (Mat Black)

Part Number Type	L	L1	Allowable Load (N)	Reference Mass (g)	USAN	USANS	USANA	USANB
80	88	2500	76					
100	108		88					
125	133		103					
160	168		125					
200	208		150					
250	258		180					

Ordering Example: Part Number
 USAN80

U-Shaped Square Bar

USANK

Material	Surface Treatment
Zinc Alloy	Chrome Plating

Part Number Type	L	L1	W	H	B	S	M (Coarse)	Reference Mass (g)	Unit Price
65	76	12	30	8	8	M5	55		
100	108	14	30	8	8	M5	80		
110	120	16	40	10	8	M6	130		
120	130	16	40	10	8	M6	145		
188	200	18	50	12	10	M8	250		

Ordering Example: Part Number
 USANK100

Square Bar Pull Handles - L Configurable

USANSF

Part Number Type	L 1mm Increment	Allowable Load (N)	Unit Price
USANSF	80-125	2500	
	126-250		
	251-300		

Ordering Example: Part Number - L
 USANSF - 85